



MSR

MSR 700/2 1CT/8

MSR – bright vivid colours, always The high colour rendering index of the single ended MSR series ensures that everyone in the audience can enjoy the true colours of the scenery, the stage props, the players and their costumes – in fact everything that is on stage can be made bright and vivid in daylight quality light. Also, thanks to the single ended lamp concept, the luminaire has optimal light collection and direction possibilities to help ensure brightness on stage exactly where and when it is needed. In addition, the MSR can be used in any burning position for easy set-up and convenience.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


Product data

General Information			
Cap-Base	G22 [G22]	Luminous Efficacy (rated) (Nom)	78 lm/W
Operating Position	UNIVERSAL [Any or Universal (U)]	Color rendering index (CRI)	80
Life to 50% Failures (Nom)	1,000 hour(s)	Arc Length O (Nom)	8.0 mm
Light Technical		Operating and Electrical	
Color Code	2	Power Consumption	700 W
Luminous Flux	55,000 lm	Lamp Current (Nom)	11 A
Chromaticity Coordinate X (Nom)	302	Controls and Dimming	
Chromaticity Coordinate Y (Nom)	320	Dimmable	No
Correlated Color Temperature (Nom)	7200 K		

Product Data	
Order product name	MSR 700/2 1CT/8
Full product name	MSR 700/2 1CT/8
Full product code	872790091638600
Order code	928171505114
Material Nr. (12NC)	928171505114


Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8727900916386
Numerator - Packs per outer box	8
EAN/UPC - Case	8727900916393

Dimensional drawing



Product	D (max)	O	L (min)	L (max)	L	C (max)	F
MSR 700/2 1CT/8	30 mm	8.0 mm	74 mm	76 mm	75 mm	152 mm	42 mm

Photometric data



Spectral Power Distribution Colour - MSR 700/2 1CT/8

