



MSD

MSD 150/2 1CT/4

These single ended, compact lamps enable optimal light collection and accurate beam control, while they also provide true daylight color temperatures – all to create great stage brightness and vivid entertainment. And since they offer long lifetime usage they help minimize the cost of ownership via fewer lamp replacements and fewer maintenance man hour costs.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Product data


General Information	
Cap-Base	G12 [G12]
Operating Position	UNIVERSAL [Any or Universal (U)]
Life to 50% Failures (Nom)	3,000 hour(s)
Light Technical	
Color Code	2
Luminous Flux (Min)	9,450 lm
Luminous Flux	10,500 lm
Chromaticity Coordinate X (Nom)	287
Chromaticity Coordinate Y (Nom)	301
Correlated Color Temperature (Nom)	8790 K
Luminous Efficacy (rated) (Nom)	70 lm/W
Color rendering index (CRI)	58

Arc Length O (Nom)	5.0 mm
Operating and Electrical	
Power Consumption	150 W
Lamp Current (Nom)	1.85 A
Controls and Dimming	
Dimmable	No
Product Data	
Order product name	MSD 150/2. 1CT/4
Full product name	MSD 150/2 1CT/4
Full product code	871869641598600
Order code	261396

Material Nr. (12NC)	928172805115
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696415986
Numerator - Packs per outer box	4


EAN/UPC - Case	8718696415993
----------------	---------------

Dimensional drawing



Product	D (max)	O	L (min)	L (max)	L	C (max)
MSD 150/2. 1CT/4	13/16 inch	1/4 inch	2-3/16 inch	2-1/4 inch	2-1/4 inch	4-3/8 inch

Photometric data



Spectral Power Distribution Colour - MSD 150/2. 1CT/4

