



# MSR Gold™ SA Double Ended

## MSR Gold 700 SA/2 DE 1CT/4

To optimize the total lifetime of the double ended MSR Gold™ SA Double Ended lamps, the caps are plated with gold. This provides superior heat protection and thereby minimizes premature failure of the lamp and lamp holder, as well as ensuring extended consistent performance. In addition, the highly innovative P3 technology, developed by Philips, allows the lamp to be used at higher temperatures, which further extends service life and consistency of high-quality light output.

#### **Warnings and Safety**

• A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

#### **Product data**

General Information			
Cap-Base	SFC10-4		
Operating Position	UNIVERSAL [Any or Universal (U)]		
Life to 50% Failures (Nom)	750 hour(s)		
Light Technical			
Color Code	- [Not Specified]		
Luminous Flux	48,000 lm		
Chromaticity Coordinate X (Nom)	299		
Chromaticity Coordinate Y (Nom)	320		
Correlated Color Temperature (Nom)	7500 K		
Luminous Efficacy (Rated) (Min)	62 lm/W		
Luminous Efficacy (rated) (Nom)	69 lm/W		

Color rendering index (CRI)	73				
Arc Length O (Nom)	4.0 mm				
Operating and Electrical					
Power Consumption	700 W				
Lamp Current (Nom)	11.5 A				
Controls and Dimming					
Dimmable	No				
Product Data					
Order product name	MSR Gold 700 SA/2 DE 1CT/4				
Full product name	MSR Gold 700 SA/2 DE 1CT/4				


Datasheet, 2024, February 1 data subject to change

### MSR Gold™ SA Double Ended

Full product code	871829122123400
Order code	928174705115
Material Nr. (12NC)	928174705115
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291221234


Numerator - Packs per outer box	4
EAN/UPC - Case	8718291221241

#### Dimensional drawing



Product	D (max)	0	A (min)	A (max)	Α	C (max)
MSR Gold 700 SA/2 DE	19 mm	4.0 mm	114.4 mm	115.2 mm	114.8 mm	136 mm
1CT/4						

#### Photometric data



Spectral Power Distribution Colour - MSR Gold 700 SA/2 DE 1CT/4



© 2024 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.