



MSR Gold™ FastFit

MSR Gold™ 1200 FastFit 1CT/4

All lamps burn out eventually, but when this happens with single ended MSR Gold™ FastFit, it is replaced in seconds – thanks to the specially designed lamp base and lamp holder. This lamp provides a high beam intensity of pure, white light for a truly illuminating performance, while the gold-plated caps provide superior heat protection and prevent premature failure. P3 technology allows use in any position and at higher temperatures, further extending lamp life and consistency of high-quality light output. Also, because the FastFit design is applied to Philips Halogen lamps, switching between lamp technologies can be done quickly and easily. The Philips MSR Gold™ 1200 FastFit can be operated in a lamp wattage range between 800W and 1400W.

Product data

General Information		Operating and Electrical	
Cap base	PGJX50 [PGJX50]	Power (Rated) (Nom)	1200 W
Operating position	UNIVERSAL [Any or Universal (U)]	Lamp current (nom.)	15 A
Main application	Entertainment	Ignition supply voltage (min.)	198 V
Life to 50% failures (nom.)	750 h		
System description	FastFit	Controls and Dimming	
		Dimmable	Yes
Light Technical		Mechanical and Housing	
Colour code	- [Not Specified]	Cap base information	PGJX50
Luminous flux (min.)	79500 lm	Luminaire Design Requirements	
Luminous flux (nom.)	95000 lm	Bulb temperature (max.)	950 °C
Chromaticity coordinate X (nom.)	318	Pinch temperature (max.)	500 °C
Chromaticity coordinate Y (nom.)	327		
Correlated Colour Temperature (Nom)	6000 K	Product Data	
Luminous efficacy (rated) (nom.)	80 lm/W	Full product code	871829122129600
Color rendering index (nom.)	80		


MSR Gold™ FastFit

Order product name	MSR Gold™ 1200 FastFit 1CT/4
EAN/UPC – product	8718291221296
Order code	22129600
Numerator – quantity per pack	1
Numerator – packs per outer box	4

Material no. (12NC)	928175005115
Net weight (piece)	0.147 kg

Warnings and Safety

Dimensional drawing



MSR GOLD 1200 FastFit

Product

MSR Gold™ 1200 FastFit 1CT/4

