



# MSR Gold™ FastFit

## MSR Gold 1200 FastFit 1CT/4

All lamps burn out eventually, but when this happens with single ended MSR Gold™ FastFit, it is replaced in seconds – thanks to the specially designed lamp base and lamp holder. This lamp provides a high beam intensity of pure, white light for a truly illuminating performance, while the gold-plated caps provide superior heat protection and prevent premature failure. P3 technology allows use in any position and at higher temperatures, further extending lamp life and consistency of high-quality light output. Also, because the FastFit design is applied to Philips Halogen lamps, switching between lamp technologies can be done quickly and easily. The Philips MSR Gold<sup>TM</sup> 1200 FastFit can be operated in a lamp wattage range between 800W and 1400W.

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data

General Information	
Cap-Base	PGJX50
Operating Position	UNIVERSAL [Any or Universal (U)]
Life to 50% Failures (Nom)	750 h
Light Technical	
Color Code	- [Not Specified]
Luminous Flux	100,000 lm
Chromaticity Coordinate X (Nom)	318
Chromaticity Coordinate Y (Nom)	327
Correlated Color Temperature (Nom)	6000 K
Luminous Efficacy (rated) (Nom)	83 lm/W


Color rendering index (CRI)	80
Arc Length O (Nom)	5.5 mm
Operating and Electrical	
Power Consumption	1,200 W
Lamp Current (Nom)	15 A
Controls and Dimming	
Dimmable	Yes
Product Data	
Order product name	MSR Gold 1200 FastFit 1CT/4

MSR Gold™ FastFit

Full product name	MSR Gold 1200 FastFit 1CT/4
Full product code	871829122129600
Local code description	MSRG1200FF
Order code	928175005115
Material Nr. (12NC)	928175005115
Local order code	MSRG1200FF

Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291221296
Numerator - Packs per outer box	4
EAN/UPC - Case	8718291221302

Dimensional drawing



Product	D (max)	O	L (min)	L (max)	L	C (max)	F
MSR Gold 1200 FastFit 1CT/4	26.1 mm	5.5 mm	64 mm	66 mm	65 mm	128 mm	50 mm

