



MSR Gold™ FastFit

MSR Gold 1200 FastFit 1CT/4

All lamps burn out eventually, but when this happens with single ended MSR Gold™ FastFit, it is replaced in seconds – thanks to the specially designed lamp base and lamp holder. This lamp provides a high beam intensity of pure, white light for a truly illuminating performance, while the gold-plated caps provide superior heat protection and prevent premature failure. P3 technology allows use in any position and at higher temperatures, further extending lamp life and consistency of high-quality light output. Also, because the FastFit design is applied to Philips Halogen lamps, switching between lamp technologies can be done quickly and easily. The Philips MSR Gold™ FastFit can be operated in a lamp wattage range between 700W and 2500W.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


General Information		Color rendering index (CRI)	
Cap-Base	PGJX50 [PGJX50]	Arc Length O (Nom)	5.5 mm
Operating Position	UNIVERSAL [Any or Universal (U)]	Operating and Electrical	
Life to 50% Failures (Nom)	750 hour(s)	Power Consumption	1,200 W
Light Technical		Lamp Current (Nom)	15 A
Color Code	- [Not Specified]	Controls and Dimming	
Luminous Flux	100,000 lm	Dimmable	Yes
Chromaticity Coordinate X (Nom)	318	Product Data	
Chromaticity Coordinate Y (Nom)	327	Order product name	MSR Gold 1200 FastFit 1CT/4
Correlated Color Temperature (Nom)	6000 K		
Luminous Efficacy (rated) (Nom)	83 lm/W		

MSR Gold™ FastFit

Full product name	MSR Gold 1200 FastFit 1CT/4
Full product code	871829122129600
Order code	928175005115
Material Nr. (12NC)	928175005115
Local order code	MSRG1200FF
Numerator - Quantity Per Pack	1

EAN/UPC - Product/Case	8718291221296
Numerator - Packs per outer box	4
EAN/UPC - Case	8718291221302

Dimensional drawing



Product	D (max)	O	L (min)	L (max)	L	C (max)	F
MSR Gold 1200 FastFit 1CT/4	26.1 mm	5.5 mm	64 mm	66 mm	65 mm	128 mm	50 mm

