



MSR Gold™ FastFit

MSR Gold™ 1200 FastFit 1CT/4

All lamps burn out eventually, but when this happens with single ended MSR Gold™ FastFit, it is replaced in seconds – thanks to the specially designed lamp base and lamp holder. This lamp provides a high beam intensity of pure, white light for a truly illuminating performance, while the gold-plated caps provide superior heat protection and prevent premature failure. P3 technology allows use in any position and at higher temperatures, further extending lamp life and consistency of high-quality light output. Also, because the FastFit design is applied to Philips Halogen lamps, switching between lamp technologies can be done quickly and easily. The Philips MSR GoldTM 1200 FastFit can be operated in a lamp wattage range between 800W and 1400W.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Product data


| General Information | | | |
|---------------------------------|----------------------------------|------------------------------------|---------|
| Cap-Base | PGJX50 | Correlated Color Temperature (Nom) | 6000 K |
| Operating Position | UNIVERSAL [Any or Universal (U)] | Luminous Efficacy (rated) (Nom) | 83 lm/W |
| Life to 50% Failures (Nom) | 750 hour(s) | Color rendering index (CRI) | 80 |
| | | Arc Length O (Nom) | 5.5 mm |
| Light Technical | | Operating and Electrical | |
| Color Code | - [Not Specified] | Power Consumption | 1,200 W |
| Luminous Flux | 100,000 lm | Lamp Current (Nom) | 15 A |
| Chromaticity Coordinate X (Nom) | 318 | | |
| Chromaticity Coordinate Y (Nom) | 327 | | |

MSR Gold™ FastFit

| Controls and Dimming | |
|----------------------|------------------------------|
| Dimmable | Yes |
| Product Data | |
| Order product name | MSR Gold 1200 FastFit 1CT/4 |
| Full product name | MSR Gold™ 1200 FastFit 1CT/4 |
| Full product code | 871829122129600 |
| Order code | 286880 |

| | |
|---------------------------------|---------------|
| Material Nr. (12NC) | 928175005115 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8718291221296 |
| Numerator - Packs per outer box | 4 |
| EAN/UPC - Case | 8718291221302 |

Dimensional drawing



| Product | D (max) | O | L (min) | L (max) | L | C (max) | F |
|--------------|---------|------|---------|---------|--------|---------|--------|
| MSR Gold | 1-1/16 | 1/4 | 2-9/16 | 2-5/8 | 2-9/16 | 5-1/16 | 2 inch |
| 1200 FastFit | inch | inch | inch | inch | inch | inch | |
| 1CT/4 | | | | | | | |

