

PHILIPS

Lighting



MSR Gold™ SA Double Ended

MSR Gold™ 575 SA/2 DE 1CT/40

To optimize the total lifetime of the double ended MSR Gold™ SA Double Ended lamps, the caps are plated with gold. This provides superior heat protection and thereby minimizes premature failure of the lamp and lamp holder, as well as ensuring extended consistent performance. In addition, the highly innovative P3 technology, developed by Philips, allows the lamp to be used at higher temperatures, which further extends service life and consistency of high-quality light output.

Product data

| General Information | |
|----------------------------|------------------------|
| Base | SFC-11 [SFC-11] |
| Operating Position | Universal [Universal] |
| Main Application | Entertainment |
| Life to 50% Failures (Nom) | 7500 h |
| System Description | SA/2 DE |

| Light Technical | |
|------------------------------------|----------|
| Color Code | 2 |
| Initial lumen (Min) | 39000 lm |
| Initial lumen (Nom) | 42000 lm |
| Chromaticity Coordinate X (Nom) | 294 |
| Chromaticity Coordinate Y (Nom) | 317 |
| Correlated Color Temperature (Nom) | 7500 K |
| Luminous Efficacy (rated) (Nom) | 73 lm/W |
| Color Rendering Index (Nom) | 75 |

| Operating and Electrical | |
|-------------------------------|-------|
| Power (Rated) (Nom) | 575 W |
| Lamp Current (Nom) | 7 A |
| Ignition Supply Voltage (Min) | 198 V |

| Controls and Dimming | |
|----------------------|----|
| Dimmable | No |

| Mechanical and Housing | |
|------------------------|--------|
| Cap-Base Information | SFC-11 |

| Luminaire Design Requirements | |
|-------------------------------|--------|
| Pinch Temperature (Max) | 400 °C |

| Product Data | |
|--------------------|------------------------------|
| Order product name | MSR Gold™ 575 SA/2 DE 1CT/40 |
| EAN/UPC - Product | 8727900914641 |
| Order code | 245019 |

MSR Gold™ SA Double Ended


| | |
|---------------------------------|--------------|
| Numerator - Quantity Per Pack | 1 |
| Numerator - Packs per outer box | 40 |
| Material Nr. (12NC) | 928175105114 |

| | |
|--------------------|----------|
| Net Weight (Piece) | 0.032 kg |
|--------------------|----------|

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Lamp contains mercury. Manage in Accord with Disposal Laws. See: www.lamprecycle.org or 1-800-555-0050


Dimensional drawing



MSR GOLD 575 SA/2 DE

| Product | D (max) | O | A (min) | A (max) | A | C (max) |
|-----------------------|---------|--------|---------|---------|-------|---------|
| MSR Gold™ 575 SA/2 DE | 18.5 mm | 5.0 mm | 69.6 mm | 70.4 mm | 70 mm | 92 mm |
| 1CT/40 | | | | | | |

Photometric data



XDPB_XDMSR_575W_SA2-DE-Spectral power distribution B/W

