

Lighting

PHILIPS

MSR Gold™ SA Double Ended

MSR Gold 1510 SA/DE 1CT/4

To optimize the total lifetime of the double ended MSR Gold[™] SA Double Ended lamps, the caps are plated with gold. This provides superior heat protection and thereby minimizes premature failure of the lamp and lamp holder, as well as ensuring extended consistent performance. In addition, the highly innovative P3 technology, developed by Philips, allows the lamp to be used at higher temperatures, which further extends service life and consistency of high-quality light output.

Warnings and Safety

• A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


General Information		Arc Length O (Nom)	7.0 mm	
Cap-Base	SFC10-4			
Operating Position	UNIVERSAL [Any or Universal (U)]	Operating and Electrical		
Life to 50% Failures (Nom)	750 hour(s)	Power Consumption	1,510 W	
		Lamp Current (Nom)	13.5 A	
Light Technical				
Color Code	- [Not Specified]	Controls and Dimming		
Luminous Flux	140,000 lm	Dimmable	Yes	
Chromaticity Coordinate X (Nom)	326			
Chromaticity Coordinate Y (Nom)	336	Product Data		
Correlated Color Temperature (Nom)	6000 K	Order product name MSR Gold 1510 SA/DE 10		
Luminous Efficacy (rated) (Nom)	93 lm/W	Full product name MSR Gold 1510 SA/DE 10		
Color rendering index (CRI)	85	Full product code	871829122113500	

MSR Gold[™] SA Double Ended

Order code	928176605115	
Material Nr. (12NC)	928176605115	
Numerator - Quantity Per Pack	1	
EAN/UPC - Product/Case	8718291221135	


Numerator - Packs per outer box	4
EAN/UPC - Case	8718291221142

Dimensional drawing



Product	D (max)	0	А	C (max)
MSR Gold 1510 SA/DE 1CT/4	23.2 mm	7.0 mm	114.8 mm	136 mm

Photometric data



Spectral Power Distribution Colour - MSR Gold 1510 SA/DE 1CT/4



© 2024 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com 2024, February 8 - data subject to change