



MSR Gold™ FastFit

MSR Gold™ 2000 FastFit 1CT/8

All lamps burn out eventually, but when this happens with single ended MSR Gold™ FastFit, it is replaced in seconds – thanks to the specially designed lamp base and lamp holder. This lamp provides a high beam intensity of pure, white light for a truly illuminating performance, while the gold-plated caps provide superior heat protection and prevent premature failure. P3 technology allows use in any position and at higher temperatures, further extending lamp life and consistency of high-quality light output. Also, because the FastFit design is applied to Philips Halogen lamps, switching between lamp technologies can be done quickly and easily. The Philips MSR Gold™ FastFit can be operated in a lamp wattage range between 700W and 2500W.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information		Operating and Electrical	
Cap-Base	PGJX50 [PGJX50]	Power (Nom)	2000 W
Operating Position	UNIVERSAL [Any or Universal (U)]	Lamp Current (Nom)	15.2 A
Main Application	Entertainment	Ignition Supply Voltage (Min)	198 V
Life to 50% Failures (Nom)	750 h	Chromaticity Coordinate Y (Nom)	332
System Description	FastFit	Correlated Color Temperature (Nom)	6050 K
Light Technical		Luminous Efficacy (rated) (Nom)	90 lm/W
Color Code	- [Not Specified]	Color Rendering Index (Nom)	91
Luminous Flux (Min)	162000 lm		
Luminous Flux (Nom)	180000 lm		
Chromaticity Coordinate X (Nom)	321		

MSR Gold™ FastFit

Controls and Dimming

Dimmable	Yes
----------	-----

Mechanical and Housing

Cap-Base Information	PGJX50
----------------------	--------

Luminaire Design Requirements

Bulb Temperature (Max)	950 °C
Pinch Temperature (Max)	500 °C

Product Data

Full product code	872790091949300
-------------------	-----------------

Order product name	MSR Gold™ 2000 FastFit 1CT/8
EAN/UPC - Product	8727900919493
Order code	928176905114
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	8
Material Nr. (12NC)	928176905114
Net Weight (Piece)	0.147 kg

Dimensional drawing



Product	D (max)	O	L (min)	L (max)	L	C (max)	F
MSR Gold™ 2000 FastFit 1CT/8	34 mm	8.0 mm	66 mm	68 mm	67 mm	134 mm	50 mm

MSR GOLD 2000W FastFit

