



# MSR Gold™ MiniFastFit (DJ/Club)

## MSR Gold™ 300/2 MiniFastFit 1CT/4

Thanks to the specially designed lamp base and lamp holder, the MSR Gold™ MiniFastFit takes just seconds to replace, to help ensure non-stop clubbing entertainment. In addition, the innovative gold plated pins ensure excellent current transfer to prolong lamp and lamp holder lifetimes and thereby reduce lamp replacement costs. Easy handling and small compact fixture designs are allowed by the lamps compact size, while the very short arc provides a high perceived brightness and high beam intensity.

### Product data

General Information	
Base	PGJX28 [ PGJX28]
Operating Position	Universal [ Universal]
Main Application	Entertainment
Life to 50% Failures (Nom)	750 h
System Description	MiniFastFit
Light Technical	
Color Code	2
Initial lumen (Min)	19170 lm
Initial lumen (Nom)	21300 lm
Chromaticity Coordinate X (Nom)	288
Chromaticity Coordinate Y (Nom)	306
Correlated Color Temperature (Nom)	9300 K
Luminous Efficacy (Rated) (Min)	64 lm/W
Luminous Efficacy (rated) (Nom)	71 lm/W
Color Rendering Index (Nom)	80

Operating and Electrical	
Power (Rated) (Nom)	300 W
Lamp Current (Nom)	3.75 A
Ignition Supply Voltage (Min)	207 V
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Cap-Base Information	PGJX28
Luminaire Design Requirements	
Bulb Temperature (Max)	950 °C
Pinch Temperature (Max)	500 °C
Product Data	
XUCDM.COPY.Product.Title	MSR Gold™ 300/2 MiniFastFit 1CT/4
EAN/UPC - Product	8718291221111


## MSR Gold™ MiniFastFit (DJ/Club)

Order code	287177
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	4
Material Nr. (12NC)	928177105115

Net Weight (Piece)	0.062 kg
--------------------	----------

### Warnings and Safety

### Dimensional drawing



MSR GOLD 300/2 MiniFastFit

Product	D (max)	O	L (min)	L (max)	L	C (max)
MSR Gold™ 300/2	23 mm	5.0 mm	65.8 mm	67.8 mm	66.8 mm	126 mm
MiniFastFit 1CT/4						

