



MasterColor CDM-T T6 Elite

MASTERColor CDM-T Elite 70W/930 G12 1CT

The Elite family is at the very top of the MasterColor CDM range, and gives a unique combination of unbeatable light quality and consistent performance over lifetime, while keeping running costs low. MasterColor metal halide lamps deliver consistent white light and higher color rendering than any standard metal halide source for architectural lighting.

Warnings and Safety

- R "WARNING: These lamps can cause serious skin burn and eye inflammation from short wave ultraviolet radiation if outer envelope of the lamp is broken or punctured. Do not use where people will remain for more than a few minutes unless adequate shielding or other safety precautions are used. Certain lamps that will automatically extinguish when the outer envelope is broken or punctured are commercially available." This lamp complies with FDA radiation performance standard 21 CFR subchapter J. (USA:21 CFR 1040.30 Canada: SOR/DORS/80-381)
- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Product data

General Information		Correlated Color Temperature (Nom)	
Cap-Base	G12	Correlated Color Temperature (Nom)	3000 K
Operating Position	UNIVERSAL [Any or Universal (U)]	Luminous Efficacy (rated) (Nom)	103 lm/W
Life to 50% Failures (Nom)	20,000 hour(s)	Color rendering index (CRI)	90
Light Technical		Arc Length O (Nom)	7.15 mm
Color Code	930 [CCT of 3000K]	Operating and Electrical	
Color Designation	Warm White (WW)	Power Consumption	73.2 W
Chromaticity Coordinate X (Nom)	0.435	Voltage (Nom)	85 V
Chromaticity Coordinate Y (Nom)	0.396	Voltage (Nom)	85 V

MasterColor CDM-T T6 Elite

Controls and Dimming

Dimmable	No
----------	----

Mechanical and Housing

Bulb Finish	Clear
Bulb Shape	T19


Approval and Application

Mercury (Hg) Content (Nom)	6.6 mg
Energy Consumption kWh/1000 h	80 kWh

Product Data



Order product name	MASTERCOLOR CDM-T Elite 70W/930 G12 1CT
Full product name	MASTERCOLOR CDM-T Elite 70W/930 G12 1CT
Order code	409151
Material Nr. (12NC)	928185305115
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677409159
Numerator - Packs per outer box	12
EAN/UPC - Case	50046677409154

Dimensional drawing



Product	D (max)	O	L (min)	L (max)	L	C (max)
MASTERCOLOR CDM-T	13/16 inch	5/16	2-3/16	2-1/4	2-1/4	4-1/16
Elite 70W/930 G12 1CT		inch	inch	inch	inch	inch

Photometric data





Light Distribution Diagram - MASTERCOLOR CDM-T Elite 70W/930 G12 1CT

Spectral Power Distribution Colour - MASTERCOLOR CDM-T Elite 70W/930 G12 1CT


MasterColor CDM-T T6 Elite

Lifetime



Lumen Maintenance Diagram - MASTERColor CDM-T Elite 70W/930 G12 1CT

Lumen Maintenance Diagram - MASTERColor CDM-T Elite 70W/930 G12 1CT



Life Expectancy Diagram - MASTERColor CDM-T Elite 70W/930 G12 1CT

