



MASTERColour CDM-Tm Elite Mini

MC CDM-Tm Elite Mini 35W/930 GU6.5 1CT

微型化的單端陶瓷金屬鹵化物燈管。GU6.5 轉鎖式燈座，符合全球 IEC 標準

安全提示

- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- Use only with electronic control gear
- For 50W use with Philips electronic gear only
- Control gear must include end-of-life protection (IEC61167, IEC 62035)
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

产品数据

一般資訊	
燈座基底	GU6.5
操作位置	UNIVERSAL [任何或通用 (U)]
通量測量參考	Sphere
壽命 (故障率 50%) (標稱)	20,000 h
照明技術	
色碼	930 [CCT of 3000K]
光通量	3,950 lm
色彩名稱	暖白光 (WW)
色度坐標 X (標稱)	0.434
色度坐標 Y (Nom)	0.398
相關色彩溫度 (規範)	3000 K
光效 (額定) (標準)	102 lm/W


演色性指數 (CRI)	90
電弧長 Ø (標稱)	4.7 mm
運轉與電力	
耗電量	39.1 W
電壓 (標稱)	87 V
電壓 (標稱)	87 V
控制與調光	
可調光	否
機械與外罩	
燈泡表層	透明

MASTERColour CDM-Tm Elite Mini

燈泡形狀	T13.3
認證與應用	
節能省電等級	F
汞 (Hg) 含量 (最大)	4.7 mg
汞 (Hg) 含量 (標稱)	4.7 mg
能源消耗 kWh/1000 h	40 kWh
EPREL 註冊碼	1519237
產品資料	
下訂產品名稱	MC CDM-Tm Elite Mini 35W/930 GU6.5 1CT



完整產品名稱	MC CDM-Tm Elite Mini 35W/930 GU6.5 1CT
完整產品代碼	871829115382500
訂單代碼	928187405130
材質 Nr. (12NC)	928187405130
分子 - 每個包裝的數量	1
EAN/UPC - 產品/案例	8718291153825
分子 - 每一外盒包裝	12
EAN/UPC - 箱	8718291153832

二维绘图



Product	D (max)	D	O	L (min)	L (max)	L	C (max)
MC CDM-Tm Elite Mini 35W/930 GU6.5 1CT	13.3 mm	0.5 in	4.7 mm	28 mm	32 mm	30 mm	56.7 mm

光度数据




Light Distribution Diagram - MC CDM-Tm Elite Mini 35W/930 GU6.5 1CT


Spectral Power Distribution Colour - MC CDM-Tm Elite Mini 35W/930 GU6.5 1CT

MASTERColour CDM-Tm Elite Mini

壽命



Life Expectancy Diagram - MC CDM-Tm Elite Mini 35W/930 GU6.5 1CT



Lumen Maintenance Diagram - MC CDM-Tm Elite Mini 35W/930 GU6.5 1CT

