



MASTERColour CDM-TC Elite

MASTERC CDM-TC Elite 70W/930 G8.5 1CT/12

體積精巧，高效率的單端陶瓷金屬鹵化物放電燈管

安全提示

- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- Use only with electronic control gear
- Control gear must include end-of-life protection (IEC61167, IEC 62035)
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

产品数据

一般資訊	
燈座基底	G8.5
操作位置	UNIVERSAL [任何或通用 (U)]
壽命 (故障率 50%) (標稱)	20,000 h
照明技術	
色碼	930 [CCT of 3000K]
色彩名稱	暖白光 (WW)
色度坐標 X (標稱)	0.435
色度坐標 Y (Nom)	0.396
相關色彩溫度 (規範)	3000 K
光效 (額定) (標準)	107 lm/W
演色性指數 (CRI)	90
電弧長 O (標稱)	7.15 mm


運轉與電力	
耗電量	73.2 W
電壓 (標稱)	85 V
電壓 (標稱)	85 V
控制與調光	
可調光	否
機械與外罩	
燈泡表層	透明
燈泡形狀	T14
認證與應用	
汞 (Hg) 含量 (標稱)	6.6 mg

MASTERC colour CDM-TC Elite

能源消耗 kWh/1000 h	80 kWh
產品資料	
下訂產品名稱	MASTERC CDM-TC Elite 70W/930 G8.5 1CT/12
完整產品名稱	MASTERC CDM-TC Elite 70W/930 G8.5 1CT/12
完整產品代碼	871869648471500
訂單代碼	928189505129


材質 Nr. (12NC)	928189505129
分子 - 每個包裝的數量	1
EAN/UPC - 產品/案例	8718696484715
分子 - 每一外盒包裝	12
EAN/UPC - 箱	8718696484722

二维绘图




Product	D (max)	O	L (min)	L (max)	L	C (max)
MASTERC CDM-TC Elite 70W/930 G8.5 1CT/12	15 mm	7.15 mm	51 mm	53 mm	52 mm	85 mm

光度数据




Light Distribution Diagram - MASTERC CDM-TC Elite 70W/930 G8.5 1CT/12




Spectral Power Distribution Colour - MASTERC CDM-TC Elite 70W/930 G8.5 1CT/12

MASTERC colour CDM-TC Elite

壽命



Lumen Maintenance Diagram - MASTERC CDM-TC Elite 70W/930 G8.5 1CT/12



Life Expectancy Diagram - MASTERC CDM-TC Elite 70W/930 G8.5 1CT/12

