



MASTERColour CDM-T Elite



MASTERColour CDM-T Elite 50W/930 G12 1CT/12

Single-ended, high-efficiency Ceramic Metal Halide discharge lamp

Warnings and Safety

- · Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- \cdot The luminaire must be able to contain hot lamp parts if the lamp ruptures
- · Use only with electronic control gear. 35W & 70W lamps may also use electromagnetic gear.
- · Control gear must include end-of-life protection (IEC61167, IEC 62035)
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information						
Cap base	G12					
Operating position	UNIVERSAL [Any or Universal (U)]					
Flux measurement reference	Sphere					
Life to 50% failures (nom.)	20,000 h					
Light Technical						
Colour Code	930 [CCT of 3000K]					
Luminous Flux	5,450 lm					
Colour designation	Warm White (WW)					
Chromaticity Coordinate X (Nom)	0.434					
Chromaticity Coordinate Y (Nom)	0.398					
Correlated Colour Temperature	3000 K					
Luminous efficacy (rated) (nom.)	108 lm/W					
Colour rendering index (CRI)	90					

Arc Length O (Nom)	6 mm
Operating and Electrical	
Power Consumption	50.2 W
Voltage (nom.)	90 V
Voltage (nom.)	90 V
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Lamp Finish	Clear
Bulb shape	T19 [T 19 mm]


Datasheet, 2023, April 16 data subject to change

MASTERColour CDM-T Elite

Approval and Application				
Energy Efficiency Class	F			
Mercury (Hg) content (max.)	6.6 mg			
Mercury (Hg) content (nom.)	6.6 mg			
Energy consumption kWh/1,000 hours 51 kWh				
EPREL registration number	473269			
Product Data				
Order product name	MASTERC CDM-T Elite 50W/930 G12 1CT/12			
Full product name	MASTERColour CDM-T Elite 50W/930 G12			
	1CT/12			


Full EOC	872790093060300				
Order code	93060300				
Material no. (12 NC)	928191705131				
Local order code	50CDMTELITE930				
SAP numerator – quantity per pack	1				
EAN/UPC — Product/Case	8727900930603				
Numerator – packs per outer box	12				
EAN/UPC - Case	8727900930610				

Dimensional drawing



Product	D (max)	0	L (min)	L (max)	L	C (max)
MASTERC CDM-T Elite 50W/930	20 mm	6 mm	55 mm	57 mm	56 mm	103 mm
G12 1CT/12						


Photometric data




Spectral Power Distribution Colour - MASTERC CDM-T Elite 50W/930 G12 1CT/12

MASTERColour CDM-T Elite

Lifetime





Lumen Maintenance Diagram - MASTERC CDM-T Elite 50W/930 G12 1CT/12

Life Expectancy Diagram - MASTERC CDM-T Elite 50W/930 G12 1CT/12



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.