



MASTERColour CDM-TC Elite

MASTERC CDM-TC Elite 50W/930 G8.5 1CT/12

體積精巧，高效率的單端陶瓷金屬鹵化物放電燈管

安全提示

- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- Use only with electronic control gear
- Control gear must include end-of-life protection (IEC61167, IEC 62035)
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

产品数据

一般資訊	
燈座基底	G8.5
操作位置	UNIVERSAL [任何或通用 (U)]
通量測量參考	Sphere
壽命 (故障率 50%) (標稱)	20,000 h
照明技術	
色碼	930 [CCT of 3000K]
光通量	5,400 lm
色彩名稱	暖白光 (WW)
色度坐標 X (標稱)	0.434
色度坐標 Y (Nom)	0.398
相關色彩溫度 (規範)	3000 K
光效 (額定) (標準)	108 lm/W
演色性指數 (CRI)	91


電弧長 Ø (標稱)	6 mm
運轉與電力	
耗電量	50.2 W
電壓 (標稱)	90 V
電壓 (標稱)	90 V
控制與調光	
可調光	否
機械與外罩	
燈泡表層	透明
燈泡形狀	T14

MASTERC colour CDM-TC Elite

認證與應用	
節能省電等級	F
汞 (Hg) 含量 (最大)	6.6 mg
汞 (Hg) 含量 (標稱)	6.6 mg
能源消耗 kWh/1000 h	51 kWh
EPREL 註冊碼	473270
產品資料	
下訂產品名稱	MASTERC CDM-TC Elite 50W/930 G8.5 1CT/12
完整產品名稱	MASTERC CDM-TC Elite 50W/930 G8.5 1CT/12


完整產品代碼	872790093062700
訂單代碼	928191805131
材質 Nr. (12NC)	928191805131
分子 - 每個包裝的數量	1
EAN/UPC - 產品/案例	8727900930627
分子 - 每一外盒包裝	12
EAN/UPC - 箱	8727900930634

二维绘图



Product	D (max)	O	L (min)	L (max)	L	C (max)
MASTERC CDM-TC Elite 50W/930 G8.5 1CT/12	15 mm	6 mm	51 mm	53 mm	52 mm	85 mm


光度数据




Spectral Power Distribution Colour - MASTERC CDM-TC Elite 50W/930 G8.5 1CT/12

MASTERC colour CDM-TC Elite

壽命



Lumen Maintenance Diagram - MASTERC CDM-TC Elite 50W/930 G8.5 1CT/12



Life Expectancy Diagram - MASTERC CDM-TC Elite 50W/930 G8.5 1CT/12

