



# MSR Gold™ MiniFastFit (Touring/ Stage)

## MSR Gold™ 400 MiniFastFit 1CT/16

Thanks to the specially designed lamp base, the MSR Gold™ MiniFastFit takes just seconds to replace, to help ensure non-stop clubbing entertainment. In addition, the innovative gold plated pins ensure excellent current transfer to prolong lamp and lamp holder lifetimes and thereby reduce lamp replacement costs. Easy handling and small compact fixture designs are allowed by the lamps compact size, while the very short arc provides a high perceived brightness and high beam intensity.

### Product data

General Information		Colour Rendering Index,horiz (Nom)	
Cap base	PGJX28 [ PGJX28]		60
Burning Position	UNIVERSAL [ Any/Universal]	Operating and Electrical	
Main application	Entertainment	Power (Rated) (Nom)	400 W
Life to 50% failures (nom.)	750 h	Lamp current (nom.)	7.2 A
System description	MiniFastFit	Ignition supply voltage (min.)	198 V
Light Technical		Controls and Dimming	
Colour Code	- [ Not Specified]	Dimmable	yes
Lamp Luminous Flux 25°C EL (Min)	23400 lm	Mechanical and Housing	
Lamp Luminous Flux 25°C EL (Nom)	26000 lm	Cap base information	PGJX28
Chromaticity coordinate X (nom.)	310	Luminaire Design Requirements	
Chromaticity coordinate Y (nom.)	320	Bulb temperature (max.)	950 °C
Colour Temperature, horizontal (Nom)	6700 K		
Lamp Luminous Efficacy EM (Nom)	65 lm/W		


## MSR Gold™ MiniFastFit (Touring/Stage)

Pinch temperature (max.)	500 °C
<b>Product Data</b>	
Full product code	871829115828800
Order product name	MSR Gold™ 400 MiniFastFit 1CT/16
EAN/UPC – product	8718291158288
Order code	928194005114

Local Code	MSR400MINIFAST
Numerator – quantity per pack	1
Numerator – packs per outer box	16
Material no. (12NC)	928194005114
Net weight (piece)	0.053 kg

### Warnings and Safety

### Dimensional drawing



MSR GOLD 400 MiniFastFit

### Product

MSR Gold™ 400 MiniFastFit 1CT/16

