



MSR Gold™ MiniFastFit (Touring/ Stage)

MSR Gold™ 400 MiniFastFit 1CT/16

Thanks to the specially designed lamp base, the MSR Gold™ MiniFastFit takes just seconds to replace, to help ensure non-stop clubbing entertainment. In addition, the innovative gold plated pins ensure excellent current transfer to prolong lamp and lamp holder lifetimes and thereby reduce lamp replacement costs. Easy handling and small compact fixture designs are allowed by the lamps compact size, while the very short arc provides a high perceived brightness and high beam intensity.

Product data

General Information		Color Rendering Index (Nom)	
Base	PGJX28 [PGJX28]		60
Operating Position	Universal [Universal]	Operating and Electrical	
Main Application	Entertainment	Power (Rated) (Nom)	400 W
Life to 50% Failures (Nom)	750 h	Lamp Current (Nom)	7.2 A
System Description	MiniFastFit	Ignition Supply Voltage (Min)	198 V
Light Technical		Controls and Dimming	
Color Code	- [Not Specified]	Dimmable	Yes
Initial lumen (Min)	23400 lm	Mechanical and Housing	
Initial lumen (Nom)	26000 lm	Cap-Base Information	PGJX28
Chromaticity Coordinate X (Nom)	310	Luminaire Design Requirements	
Chromaticity Coordinate Y (Nom)	320	Bulb Temperature (Max)	950 °C
Correlated Color Temperature (Nom)	6700 K		
Luminous Efficacy (rated) (Nom)	65 lm/W		


MSR Gold™ MiniFastFit (Touring/Stage)

Pinch Temperature (Max)	500 °C
Product Data	
Order product name	MSR Gold™ 400 MiniFastFit 1CT/16
EAN/UPC - Product	8718291158288
Order code	248963

Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	16
Material Nr. (12NC)	928194005114
Net Weight (Piece)	0.053 kg

Warnings and Safety

Dimensional drawing



MSR GOLD 400 MiniFastFit

Product

MSR Gold™ 400 MiniFastFit 1CT/16

