



MASTERColour CDM-Rm Elite Mini

MASTERColour CDM-Rm Elite Mini 35W/930 GX10 MR16 40D

Mini, very high-efficiency Ceramic Metal Halide discharge reflector lamp producing crisp white sparkling light with high color rendering

Warnings and Safety

- Use only with electronic control gear
- Control gear must include end-of-life protection (IEC61167, IEC 62035).
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


General Information		Correlated Color Temperature (Nom)	3000 K
Cap-Base	GX10	Luminous Efficacy (rated) (Nom)	61 lm/W
Operating Position	UNIVERSAL [Any or Universal (U)]	Color rendering index (CRI)	90
Switching Cycle	1,350	LLMF At End Of Nominal Lifetime (Nom)	80 %
Flux measurement reference	Narrow Cone	Luminous Flux in 90° Cone (Rated)	2,150 lm
Life to 50% Failures (Nom)	15,000 hour(s)	Operating and Electrical	
Light Technical		Power Consumption	39.1 W
Color Code	930 [CCT of 3000K]	Warm-up time to 60% light	120 s
Beam Angle (Nom)	40 degree(s)	Voltage (Nom)	87 V
Luminous Flux	2,150 lm	Voltage (Nom)	87 V
Luminous Intensity (Nom)	3,600 cd		
Chromaticity Coordinate X (Nom)	0.434		
Chromaticity Coordinate Y (Nom)	0.398		

MASTERCcolour CDM-Rm Elite Mini

Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Shape	MR16
Approval and Application	
Energy Efficiency Class	G
Mercury (Hg) Content (Max)	4.7 mg
Mercury (Hg) Content (Nom)	4.7 mg
Energy Consumption kWh/1000 h	40 kWh
EPREL Registration Number	473278


Product Data	
Order product name	CDM-Rm Elite Mini 35W/930 GX10 MR16 40D
Full product name	MASTERColour CDM-Rm Elite Mini 35W/930 GX10 MR16 40D
Full product code	871829116306000
Order code	16306000
Material Nr. (12NC)	928194805330
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291163060
Numerator - Packs per outer box	12
EAN/UPC - Case	8718291163077

Dimensional drawing




Product	D (max)	D	C (max)	C	C1 (max)	A (max)
CDM-Rm Elite Mini 35W/930	51 mm	50 mm	65.4 mm	62.75 mm	60.9 mm	59 mm
GX10 MR16 40D						

Photometric data




Light Distribution Diagram - CDM-Rm Elite Mini 35W/930 GX10 MR16 40D




Spectral Power Distribution Colour - CDM-Rm Elite Mini 35W/930 GX10 MR16 40D

MASTERColour CDM-Rm Elite Mini

Lifetime



Life Expectancy Diagram - CDM-Rm Elite Mini 35W/930 GX10 MR16 40D



Lumen Maintenance Diagram - CDM-Rm Elite Mini 35W/930 GX10 MR16 40D

