# **PHILIPS** Lighting



# MSD Platinum (Touring/Stage)

## MSD Platinum 16 R UNP/24

The MSD Platinum lamps open up new levels of creative freedom in entertainment lighting, with powerful, compact and brilliantly intense light. Their compact, lightweight design provides the freedom to create smaller, lighter luminaires – for use at any location on stage. And their short arc, high color temperature and innovative reflector produce a sparkling, high beam intensity for outstanding color reproduction. They also offer long and reliable lifetime, high efficacy and fast replacement times. It all adds up to an intensely exciting creative experience.

#### Warnings and Safety

• A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

#### Product data

General Information		Arc Length O (Nom)	1.3 mm	
Cap-Base	- [-]			
Operating Position	UNIVERSAL [Any or Universal (U)]	Operating and Electrical		
Life to 50% Failures (Nom)	1,500 hour(s)	Power Consumption	330 W	
Light Technical		Controls and Dimming		
Color Code	2	Dimmable	Yes	
Luminous Flux (Min)	14,300 lm			
Luminous Flux	16,000 lm	Product Data		
Chromaticity Coordinate X (Nom)	299	Order product name	MSD Platinum 16 R UNP/24	
Chromaticity Coordinate Y (Nom)	303	Full product name	MSD Platinum 16 R UNP/24	
Correlated Color Temperature (Nom)	8000 K	Full product code	871829170377800	
Color rendering index (CRI)	-	Order code	928195205308	


### MSD Platinum (Touring/Stage)

Material Nr. (12NC)	928195205308	
Numerator - Quantity Per Pack	1	
EAN/UPC - Product/Case	8718291703778	
Numerator - Packs per outer box	24	


EAN/UPC - Case	8718291703778

#### Dimensional drawing





#### Photometric data



Spectral Power Distribution Colour - MSD Platinum 16 R UNP/24



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

Product	D (max)	0	C (max)
MSD Platinum 16 R UNP/24	58.5 mm	1.3 mm	66.4 mm

www.lighting.philips.com 2023, April 14 - data subject to change