

**PHILIPS**

Lighting



# MASTERColour CDM-R111 Elite

## MASTERColour CDM-R111 Elite CDM-R111 Elite 35W/930 GX8.5 24D

MASTERColour CDM-R111 Elite combines the trendy look of 111 mm aluminium-reflector halogen lamps with the long life, high energy efficiency and crisp white light of MASTERColour CDM.

### Product data

#### General Information

Cap base	GX8.5 [ GX8.5]
Operating position	UNIVERSAL [ Any/Universal]
Life to 5% failures (nom.)	8000 h
Life to 10% failures (nom.)	5500 h
Life to 20% failures (nom.)	10500 h
Life to 50% failures (nom.)	12000 h
ANSI code HID	C130/O
Switching cycle	1050X

#### Light Technical

Colour code	930 [ CCT of 3.000 K]
Beam Angle (Nom)	24°
Beam angle technical	23°
Beam angle technical	28°
Beam angle technical	18°
Luminous intensity (min.)	6500 cd
Luminous intensity (nom.)	8500 cd
Beam description	Narrow Flood
Colour designation	Warm white (WW)

Lumen maintenance 12,000 hours (nom.)	70 %
Lumen maintenance 2,000 hours (nom.)	90 %
Lumen maintenance 4,000 hours (nom.)	85 %
Design mean lumens	1500 lm
Chromaticity coordinate X (nom.)	0.432
Chromaticity coordinate Y (nom.)	0.392
Correlated Colour Temperature (Nom)	3000 K
Luminous efficacy (rated) (nom.)	46 lm/W
Color rendering index (min.)	87
Color rendering index (nom.)	90
LLMF at end of nominal lifetime (nom.)	70 %
Luminous Flux in 90° Cone (Rated)	1750 lm

#### Operating and Electrical


Power (Rated) (Nom)	39.1 W
Lamp current (EM) (nom.)	0.440 A
Re-ignition time (min.) (max.)	15 min
Warm-up time to 60% light (nom.)	120 s
Ignition time (max.)	30 s
Voltage (Max)	97 V

# MASTERCcolour CDM-R111 Elite

Voltage (Min)	81 V
Voltage (Nom)	89 V
<b>Controls and Dimming</b>	
Dimmable	no
Run-up time 90% (max.)	3 min
<b>Mechanical and Housing</b>	
Bulb finish	Reflector
<b>Approval and Application</b>	
Energy efficiency label (EEL)	A
Mercury (Hg) content (nom.)	4.7 mg
Energy Consumption kWh/1000 h	43 kWh

<b>Product Data</b>	
Full product code	871829168944700
Order product name	MASTERCcolour CDM-R111 Elite CDM-R111 Elite 35W/930 GX8.5 24D
EAN/UPC – product	8718291689447
Order code	68944700
Local Code	35CDMER11193024
Numerator – quantity per pack	1
Numerator – packs per outer box	6
Material no. (12NC)	928195405330
Net weight (piece)	96.000 g
ILCOS Code	MRS/UB-35/930-H-GX8.5-111/88/24


## Dimensional drawing



CDM-R111 Elite 35W/930 24D

Product	D (max)	C (max)
MASTERCcolour CDM-R111 Elite CDM-R111 Elite 35W/930 GX8.5 24D	111 mm	95 mm

## Photometric data



LDPO\_CDMR111E\_0001-Spectral power distribution Colour

1190° / 100° / 190°

## MASTERCcolour CDM-R111 Elite

