



HORTI

MASTER GREENPOWER PLUS 1000W EL/5X6CT

High Pressure Sodium lamp with clear outer bulb, optimized growthlight output and maintenance

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


Product data

General Information	
Cap-Base	K12X30S [K12x30s]
Operating Position	P [Parallel or Horizontal(HOR)]
Light Technical	
Color Code	220 [CCT of 2000K]
Chromaticity Coordinate X (Nom)	0.529
Chromaticity Coordinate Y (Nom)	0.416
Correlated Color Temperature (Nom)	2000 K
Luminous Efficacy (rated) (Nom)	141 lm/W
Color rendering index (CRI)	38
Arc Length O (Nom)	147 mm
Operating and Electrical	
Power Consumption	1,000 W
Voltage (Nom)	250 V
Voltage (Nom)	250 V

Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	T40 [T 40mm]
Approval and Application	
Mercury (Hg) Content (Nom)	42.0 mg
Energy Consumption kWh/1000 h	1116 kWh
Product Data	
Order product name	MASTER GreenPower Plus 1000W EL/5X6CT
Full product name	MASTER GREENPOWER PLUS 1000W EL/5X6CT
Full product code	872790093301700
Order code	271882
Material Nr. (12NC)	928196305116
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8727900933017
Numerator - Packs per outer box	30


EAN/UPC - Case	8727900933031
----------------	---------------

Dimensional drawing




Product	D (max)	O	C (max)	A
MASTER GreenPower Plus 1000W EL/5X6CT	33.5 mm	147 mm	394 mm	325 mm

Photometric data



Spectral Power Distribution Colour - MASTER GreenPower Plus 1000W EL/5X6CT

Lifetime



Life Expectancy Diagram - MASTER GreenPower Plus 1000W EL/5X6CT

