



Eco passport

MASTER MHN-SB

MASTER MHN-SB 2000W/956 400V K12s-7 WH HO



Energy

- Power (Rated) (Nom) : 2070.0 W
- Lamp Luminous Efficacy EM (Nom) : 108 lm/W
- Energy efficiency label (EEL) : A+
- Dimmable : no



Substances

- Mercury (Hg) content (nom.) : 215 mg



Lifetime

- Life to 10% failures (nom.) : 2300 h
- Life to 20% failures (nom.) : 3000 h
- Life to 5% failures (nom.) : 1700 h
- Life to 50% failures (nom.) : 4500 h

Our environmental product specifications overview

At Philips, we strive to make the world healthier and more sustainable through innovation. Our sustainability efforts are globally recognised and reflected, e.g. by our continuous leading positions global rankings like the Dow Jones Sustainability Index and the Carbon Disclosure Project. In our eco-design process we focus on Energy, Weight, Recycling, Packaging, Substances and Reliability to view and further improve the environmental performance of our products.

PHILIPS

2019, May 8
data subject to change
Order code : 928196805130