



MSR Gold™ MiniFastFit (Touring/ Stage)

MSR Gold™ 700/1 MiniFastFit 1CT/4

Thanks to the specially designed lamp base, the MSR Gold™ MiniFastFit takes just seconds to replace, to help ensure non-stop clubbing entertainment. In addition, the innovative gold plated pins ensure excellent current transfer to prolong lamp and lamp holder lifetimes and thereby reduce lamp replacement costs. Easy handling and small compact fixture designs are allowed by the lamps compact size, while the very short arc provides a high perceived brightness and high beam intensity.

Product data

General Information		Operating and Electrical	
Base	PGJX28 [PGJX28]	Power (Rated) (Nom)	700 W
Operating Position	Universal [Universal]	Lamp Current (Nom)	10.2 A
Main Application	Entertainment	Ignition Supply Voltage (Min)	198 V
Life to 50% Failures (Nom)	750 h		
System Description	MiniFastFit	Controls and Dimming	
		Dimmable	Yes
		Mechanical and Housing	
		Cap-Base Information	PGJX28
		Luminaire Design Requirements	
		Bulb Temperature (Max)	950 °C
		Pinch Temperature (Max)	500 °C
Light Technical			
Color Code	1		
Initial lumen (Nom)	53400 lm		
Chromaticity Coordinate X (Nom)	328		
Chromaticity Coordinate Y (Nom)	335		
Correlated Color Temperature (Nom)	5700 K		
Luminous Efficacy (rated) (Nom)	76.3 lm/W		
Color Rendering Index (Nom)	73		

MSR Gold™ MiniFastFit (Touring/Stage)


Product Data	
Order product name	MSR Gold™ 700/1 MiniFastFit 1CT/4
EAN/UPC - Product	8718291696636
Order code	292565
Numerator - Quantity Per Pack	1

Numerator - Packs per outer box	4
Material Nr. (12NC)	928197405115
Net Weight (Piece)	0.052 kg

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Lamp contains mercury. Manage in Accord with Disposal Laws. See: www.lamprecycle.org or 1-800-555-0050

Dimensional drawing



Product	D (max)	O	L (min)	L (max)	L	C (max)	F (max)	F	F (min)
MSR Gold™ 700/1 MiniFastFit 1CT/4	23.2 mm	3.8 mm	55 mm	57 mm	56 mm	112 mm	36.5 mm	36 mm	35.3 mm

MSR GOLD 700/1 MiniFastFit

