



HORTI

MASTER GreenPower Plus 750W EL UNP/50

High Pressure Sodium lamp with clear outer bulb, optimized growthlight output and maintenance

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


Product data

General Information	
Cap-Base	K12x30s
Operating Position	P [Parallel or Horizontal(HOR)]
Light Technical	
Color Code	220 [CCT of 2000K]
Chromaticity Coordinate X (Nom)	0.535
Chromaticity Coordinate Y (Nom)	0.427
Correlated Color Temperature (Nom)	2000 K
Luminous Efficacy (rated) (Nom)	152 lm/W
Color rendering index (CRI)	30
Arc Length O (Nom)	147 mm
Operating and Electrical	
Power Consumption	750.0 W
Voltage (Nom)	195 V
Voltage (Nom)	195 V

Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	T40
Approval and Application	
Mercury (Hg) Content (Nom)	35.29 mg
Energy Consumption kWh/1000 h	1020 kWh
Product Data	
Order product name	MASTER GreenPower Plus 750W EL UNP/50
Full product name	MASTER GreenPower Plus 750W EL UNP/50
Full product code	871869965471900
Order code	928198205130
Material Nr. (12NC)	928198205130
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718699654719
Numerator - Packs per outer box	50


EAN/UPC - Case	8718699654726
----------------	---------------

Dimensional drawing



Product	D (max)	O	C (max)	A
MASTER GreenPower Plus 750W EL UNP/50	33.5 mm	147 mm	394 mm	325 mm

Photometric data



Spectral Power Distribution Colour - MASTER GreenPower Plus 750W EL UNP/50

