



HORTI

HPS AGRO Plus 1000W DE EL 5X6CT

High Pressure Sodium lamp with clear outer bulb, optimized growthlight output and maintenance

Warnings and Safety


- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information	
Cap-Base	K12X30S [K12x30s]
Operating Position	P [Parallel or Horizontal(HOR)]
Light Technical	
Color Code	220 [CCT of 2000K]
Chromaticity Coordinate X (Nom)	0.537
Chromaticity Coordinate Y (Nom)	0.426
Correlated Color Temperature (Nom)	2000 K
Luminous Efficacy (rated) (Nom)	155 lm/W
Color rendering index (CRI)	30
Arc Length O (Nom)	147 mm
Operating and Electrical	
Power Consumption	1.000.0 W
Voltage (Nom)	230 V
Voltage (Nom)	230 V
Controls and Dimming	
Dimmable	Yes


Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	T40 [T 40mm]
Approval and Application	
Mercury (Hg) Content (Nom)	35.29 mg
Energy Consumption kWh/1000 h	1020 kWh
Product Data	
Order product name	HPS AGRO Plus 1000W DE EL 5X6CT
Full product name	HPS AGRO Plus 1000W DE EL 5X6CT
Order code	928198405116
Material Nr. (12NC)	928198405116
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677473914
Numerator - Packs per outer box	30
EAN/UPC - Case	50046677473919

Dimensional drawing



Product	D (max)	O	C (max)	A
HPS AGRO Plus 1000W DE EL 5X6CT	33.5 mm	147 mm	394 mm	325 mm

Photometric data



Spectral Power Distribution Colour - HPS AGRO Plus 1000W DE EL 5X6CT

Lifetime

Life Expectancy Diagram - HPS AGRO Plus 1000W DE EL 5X6CT

