



# MSD Gold™ MiniFastFit

## MSD Gold™ 300/2 MiniFastFit 1CT/16

The specially designed lamp base of the MSD Gold™ MiniFastFit means that this lamp can be replaced in just seconds, helping to ensure non-stop entertainment. In addition, the innovative gold plated pins ensure excellent current transfer to prolong lamp and lamp holder lifetimes and thereby reduce lamp replacement costs. The lamp's compact size allows for easy handling and compact fixture designs, while the very short arc provides a high perceived brightness and high beam intensity. What's more, the MSD Gold™ MiniFastFit has an extended lifetime, which further reduces lamp replacement costs.

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: [www.lamprecycle.org](http://www.lamprecycle.org) or 1-800-555-0050

### Product data


General Information			
Cap-Base	PGJX28	Chromaticity Coordinate Y (Nom)	310
Operating Position	UNIVERSAL [Any or Universal (U)]	Correlated Color Temperature (Nom)	8600 K
Life to 50% Failures (Nom)	2,000 hour(s)	Luminous Efficacy (rated) (Nom)	70 lm/W
		Color rendering index (CRI)	73
		Arc Length O (Nom)	5.0 mm
Light Technical		Operating and Electrical	
Color Code	2	Power Consumption	300 W
Luminous Flux	21,000 lm		
Chromaticity Coordinate X (Nom)	292		

MSD Gold™ MiniFastFit

Lamp Current (Nom)	3.8 A
Controls and Dimming	
Dimmable	No
Product Data	
Order product name	MSD Gold 300/2 MiniFastFit 1CT/16
Full product name	MSD Gold™ 300/2 MiniFastFit 1CT/16
Full product code	872790091257900


Order code	245381
Material Nr. (12NC)	928199805114
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8727900912579
Numerator - Packs per outer box	16
EAN/UPC - Case	8727900912586

Dimensional drawing



Product	D (max)	O	L (min)	L (max)	L	C (max)
MSD Gold 300/2	15/16 inch	1/4 inch	2-5/8 inch	2-11/16 inch	2-5/8	5 inch
MiniFastFit 1CT/16					inch	

Photometric data



Spectral Power Distribution Colour - MSD Gold 300/2 MiniFastFit 1CT/16

