



MSR Gold™ MiniFastFit (Touring/ Stage)

MSR Gold™ 700/2 MiniFastFit 1CT/4

Thanks to the specially designed lamp base, the MSR Gold™ MiniFastFit takes just seconds to replace, to help ensure non-stop clubbing entertainment. In addition, the innovative gold plated pins ensure excellent current transfer to prolong lamp and lamp holder lifetimes and thereby reduce lamp replacement costs. Easy handling and small compact fixture designs are allowed by the lamps compact size, while the very short arc provides a high perceived brightness and high beam intensity.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


| General information | | Operating and electrical | |
|----------------------------|-----------------------------------|------------------------------------|---------|
| Cap-Base | PGJX28 [PGJX28] | Power (Nom) | 700 W |
| Operating Position | UNIVERSAL [Any or Universal (U)] | Lamp Current (Nom) | 10.2 A |
| Main Application | Entertainment | Ignition Supply Voltage (Min) | 198 V |
| Life to 50% Failures (Nom) | 750 h | Chromaticity Coordinate X (Nom) | 300 |
| System Description | MiniFastFit | Chromaticity Coordinate Y (Nom) | 324 |
| Light technical | | Correlated Color Temperature (Nom) | 7200 K |
| Color Code | 2 | Luminous Efficacy (rated) (Nom) | 69 lm/W |
| Luminous Flux (Min) | 44000 lm | Color Rendering Index (Nom) | 75 |
| Luminous Flux (Nom) | 47000 lm | | |

MSR Gold™ MiniFastFit (Touring/Stage)

| Controls and dimming | |
|-------------------------------|-----------------|
| Dimmable | Yes |
| Mechanical and housing | |
| Cap-Base Information | PGJX28 |
| Luminaire design requirements | |
| Bulb Temperature (Max) | 950 °C |
| Pinch Temperature (Max) | 500 °C |
| Product data | |
| Full product code | 871829122117300 |

| | |
|---------------------------------|-----------------------------------|
| Order product name | MSR Gold™ 700/2 MiniFastFit 1CT/4 |
| EAN/UPC - Product | 8718291221173 |
| Order code | 928199905115 |
| Numerator - Quantity Per Pack | 1 |
| Numerator - Packs per outer box | 4 |
| Material Nr. (12NC) | 928199905115 |
| Net Weight (Piece) | 0.052 kg |


Dimensional drawing




MSR Gold™ 700/2 MiniFastFit 1CT/4

| Product | D (max) | O (max) | L (min) | L (max) | L (max) | C (max) | F (max) | F (max) | F (min) |
|--|------------|------------|------------|------------|------------|------------|------------|------------|------------|
| MSR Gold™ 700/2 MiniFastFit 1CT/4 | 23.2 mm | 3.8 mm | 55 mm | 57 mm | 56 mm | 112 mm | 36.5 mm | 36 mm | 35.3 mm |

Photometric data



XDPB_XDMSR_0004-Spectral power distribution B/W



MSR Gold™ MiniFastFit (Touring/Stage)

