



# Safety Starters

## S2 4-22W SER 220-240V BL LIS/12X25CT

Range of Blue glow switch starters for igniting fluorescent lamps with electromagnetic ballast 2-pin igniter in plastic (flame-retardant polycarbonate) canister and radio-interference suppression capacitor

### Produkt Daten

Allgemeine Eigenschaften	
Systembeschreibung	Tandembetrieb

  

Elektrische Kenndaten	
Power (Rated) (Nom)	4 22 W
Impulsspannung (min.)	800 V
Primärspannung (min.)	70 V
Spannung (Nom)	220-240 V

  

Systemeigenschaften	
Kondensator	Ja

  

Mechanische Kenndaten	
Gehäusefarbe	Blau

Sockelinformation	2 Pin
-------------------	-------

  

Produktdaten	
Gesamt-Produktcode	872790088644300
Bestell-Produktname	S2 4-22W SER 220-240V BL LIS/12X25CT
EAN/UPC - Produkt	8727900886443
Bestellcode	88644300
Anzahl pro Verpackung	1
Anzahl pro Umverpackung	300
Material-Nr. (12NC)	928390610114
Nettogewicht (Einzelteil)	7,000 g

## Safety Starters

### Abmessungsskizzen

F

Product	C (max)	E (max)
S2 4-22W SER 220-240V BL LIS/12X25CT	40,3 mm	21,5 mm

S2 4-22W SER 220-240V BL

