



# Ecoclick Starters

## S2 4-22W SER 220-240V WH EUR BOX/20X10

Range of premium-quality glow switch starters for igniting fluorescent lamps with electromagnetic ballast.

### Product data

General Information	
System description	Series

Operating and Electrical	
Power (Rated) (Nom)	4-22 W
Pulse voltage (min.)	800 V
Non-reclosure voltage (min.)	70 V
Voltage (Nom)	220-240 V

System characteristics	
Capacitor	yes

Mechanical and Housing	
Housing colour	White


Cap base information	2P
----------------------	----

Product Data	
Full product code	871150069750931
Order product name	S2 4-22W SER 220-240V WH EUR BOX/20X10
EAN/UPC – product	8711500697509
Order code	69750931
Local Code	S210W
Numerator – quantity per pack	1
Numerator – packs per outer box	200
Material no. (12NC)	928390720238
Net weight (piece)	7.000 g

## Ecoclick Starters

### Dimensional drawing



S2 4-22W SER 220-240V WH EUR

Product	C (max)	E (max)
S2 4-22W SER 220-240V WH EUR BOX/20X10	40.3 mm	21.5 mm

