



Ecoclick Starters

S16 70-125W 240V UNP/20X10CT


Range of premium-quality glow switch starters for igniting fluorescent lamps with electromagnetic ballast.

Product data

Operating and Electrical	
Power Consumption	125 70 W
Voltage (Nom)	240 V
Voltage (Nom)	240 V
Mechanical and Housing	
Housing Color	White
Product Data	
Order product name	S16 70-125W 240V UNP/20X10CT
Full product name	S16 70-125W 240V UNP/20X10CT

Full product code	871150090356331
Order code	928390930371
Material Nr. (12NC)	928390930371
Local order code	S1670125W240V
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500903563
Numerator - Packs per outer box	200
EAN/UPC - Case	8711500903587

Dimensional drawing



Product	C (max)	E (max)
S16 70-125W 240V UNP/20X10CT	40.3 mm	21.5 mm