



Starters for tanning lamps

S12 115-140W 220-240V UNP/20X25CT

Range of premium-quality starters for igniting fluorescent lamps operating on electromagnetic ballasts

Warnings and Safety

- Flame-retardant components
- UV-resistant canister


Product data

Operating and Electrical	
Power Consumption	115 140 W
Voltage (Nom)	220–240 V
Mechanical and Housing	
Housing Color	Black
Product Data	
Order product name	S12 115-140W 220-240V UNP/20X25CT
Full product name	S12 115-140W 220-240V UNP/20X25CT

Full product code	871150090379226
Order code	928391630303
Material Nr. (12NC)	928391630303
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500903792
Numerator - Packs per outer box	500
EAN/UPC - Case	8711500903815

Starters for tanning lamps

Dimensional drawing



Product	C (max)	E (max)
S12 115-140W 220-240V UNP/20X25CT	40.3 mm	21.5 mm

