



Starters for tanning lamps

S12 STARTER 500 PK

Range of premium-quality starters for igniting fluorescent lamps operating on electromagnetic ballasts

Warnings and Safety

- Flame-retardant components
- · UV-resistant canister

Product data

Operating and Electrical	
Power Consumption	115 140 W
Voltage (Nom)	220-240 V
Mechanical and Housing	
Housing Color	Black
Product Data	
Order product name	S12 115-140W 220-240V UNP/20X25CT
Full product name	S12 STARTER 500 PK

Full product code	871150090379226
Order code	246991
Material Nr. (12NC)	928391630303
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500903792
Numerator - Packs per outer box	500
EAN/UPC - Case	8711500903815

Datasheet, 2023, August 28 data subject to change

Starters for tanning lamps

Dimensional drawing



Product	C (max)	E (max)
S12 115-140W 220-240V UNP/20X25CT	1-5/8 inch	7/8 inch



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.