

# Starters for tanning lamps

## S12 STARTER 500 PK

Range of premium-quality starters for igniting fluorescent lamps operating on electromagnetic ballasts

### Product data

General Information	
System Description	Single

Operating and Electrical	
Power (Rated) (Nom)	115-140 W
Pulse Voltage (Min)	600 V
Non Reclosure Voltage (Min)	135 V
Voltage (Nom)	220-240 V

System characteristics	
Capacitor	Yes

Mechanical and Housing	
Housing Color	Black

Cap-Base Information	2P
----------------------	----


  

Product Data	
Order product name	S12 115-140W 220-240V UNP/20X25CT
EAN/UPC - Product	8711500903792
Order code	246991
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	500
Material Nr. (12NC)	928391630303
Net Weight (Piece)	7.000 g

### Warnings and Safety

## Starters for tanning lamps

### Dimensional drawing



S12 115-140W SIN 220-240V BK

Product	C (max)	E (max)
S12 115-140W 220-240V UNP/20X25CT	40.3 mm	21.5 mm

