



Ecoclick Starters

S10 4-65W SIN 220-240V WH EUR/12X25CT


Range of premium-quality glow switch starters for igniting fluorescent lamps with electromagnetic ballast.

Product data

Operating and Electrical	
Power Consumption	4 65 W
Voltage (Nom)	220-240 V
Mechanical and Housing	
Housing Color	White
Product Data	
Order product name	S10 4-65W SIN 220-240V WH EUR/12X25CT
Full product name	S10 4-65W SIN 220-240V WH EUR/12X25CT

Full product code	871150069769133
Order code	69769133
Material Nr. (12NC)	928392220230
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500697691
Numerator - Packs per outer box	300
EAN/UPC - Case	8711500697752

Dimensional drawing



Product	C (max)	E (max)
S10 4-65W SIN 220-240V WH EUR/12X25CT	40.3 mm	21.5 mm