



Ecoclick Starters

S10 4-65W SIN 220-240V WH EUR/20X10CT

Range of premium-quality glow switch starters for igniting fluorescent lamps with electromagnetic ballast.

Product data

General Information	
System description	Single

Operating and Electrical	
Power (Rated) (Nom)	4-65 W
Pulse voltage (min.)	900 V
Non-reclosure voltage (min.)	140 V
Voltage (Nom)	220-240 V

System characteristics	
Capacitor	yes


Mechanical and Housing	
Housing colour	White

Cap base information	2P
----------------------	----

Product Data	
Full product code	871150069769131
Order product name	S10 4-65W SIN 220-240V WH EUR/20X10CT
EAN/UPC – product	8711500697691
Order code	69769131
Local Code	S1010W
Numerator – quantity per pack	1
Numerator – packs per outer box	200
Material no. (12NC)	928392220238
Net weight (piece)	7.000 g

Ecoclick Starters

Dimensional drawing



S10 4-65W SIN 220-240V WH EUR

Product	C (max)	E (max)
S10 4-65W SIN 220-240V WH EUR/20X10CT	40.3 mm	21.5 mm

