



MSR Gold™ FastFit

MSR Gold™ 2000/1 FastFit

All lamps burn out eventually, but when this happens with single ended MSR Gold™ FastFit, it is replaced in seconds – thanks to the specially designed lamp base and lamp holder. This lamp provides a high beam intensity of pure, white light for a truly illuminating performance, while the gold-plated caps provide superior heat protection and prevent premature failure. P3 technology allows use in any position and at higher temperatures, further extending lamp life and consistency of high-quality light output. Also, because the FastFit design is applied to Philips Halogen lamps, switching between lamp technologies can be done quickly and easily. The Philips MSR Gold™ 1200 FastFit can be operated in a lamp wattage range between 800W and 1400W.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Product data


General Information		Correlated Color Temperature (Nom)	
Cap-Base	PGJX50	5700 K	
Operating Position	UNIVERSAL [Any or Universal (U)]	Luminous Efficacy (rated) (Nom)	
Life to 50% Failures (Nom)	750 hour(s)	86 lm/W	
		Color rendering index (CRI)	
		90	
		Arc Length O (Nom)	
		7 mm	
Light Technical		Operating and Electrical	
Luminous Flux (Min)	155,000 lm	Power Consumption	
Luminous Flux	172,000 lm	2,000 W	
Chromaticity Coordinate X (Nom)	329	Lamp Current (Nom)	
Chromaticity Coordinate Y (Nom)	333	18.2 A	

MSR Gold™ FastFit

Controls and Dimming	
Dimmable	Yes
Product Data	
Order product name	MSR Gold 2000/1 FastFit 1CT/8
Full product name	MSR Gold™ 2000/1 FastFit
Full product code	871869667944900
Order code	323709

Material Nr. (12NC)	928410105114
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696679449
Numerator - Packs per outer box	8
EAN/UPC - Case	8718696679456

Dimensional drawing



Product	D (max)	O	L (min)	L	L	C (max)	F
MSR Gold	1-3/8	5/16	2-5/8	2-11/16	2-11/16	5-5/16	2 inch
2000/1 FastFit	inch	inch	inch	inch	inch	inch	
1CT/8							

