



MSR Gold™ FastFit

MSR Gold™ 1500/2 FastFit

All lamps burn out eventually, but when this happens with single ended MSR Gold™ FastFit, it is replaced in seconds – thanks to the specially designed lamp base and lamp holder. This lamp provides a high beam intensity of pure, white light for a truly illuminating performance, while the gold-plated caps provide superior heat protection and prevent premature failure. P3 technology allows use in any position and at higher temperatures, further extending lamp life and consistency of high-quality light output. Also, because the FastFit design is applied to Philips Halogen lamps, switching between lamp technologies can be done quickly and easily. The Philips MSR Gold™ 1200 FastFit can be operated in a lamp wattage range between 800W and 1400W.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050


Product data

General Information		Luminous Efficacy (rated) (Nom)	
Cap-Base	PGJX50 [PGJX50]	Color rendering index (CRI)	77
Operating Position	UNIVERSAL [Any or Universal (U)]	Arc Length O (Nom)	6.3 mm
Life to 50% Failures (Nom)	750 hour(s)	Operating and Electrical	
Light Technical		Power Consumption	1,500 W
Luminous Flux	116,000 lm	Lamp Current (Nom)	16.1 A
Chromaticity Coordinate X (Nom)	302		
Chromaticity Coordinate Y (Nom)	320		
Correlated Color Temperature (Nom)	7200 K		

MSR Gold™ FastFit


Controls and Dimming	
Dimmable	Yes
Product Data	
Order product name	MSR Gold 1500/2 FastFit
Full product name	MSR Gold™ 1500/2 FastFit
Full product code	871869962595500
Order code	343350
Material Nr. (12NC)	928410305115
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718699625955
Numerator - Packs per outer box	4
EAN/UPC - Case	8718699625962

Dimensional drawing



Product	D (max)	O	L (min)	L (max)	L	C (max)	F
MSR Gold	1-1/8 inch	1/4	2-9/16	2-5/8	2-9/16	5-1/16	2 inch
1500/2		inch	inch	inch	inch	inch	
FastFit							

Photometric data



Spectral Power Distribution Colour - MSR Gold 1500/2 FastFit

