

Barco digital cinema projectors


XDC 6000 B

Digital Xenon Cinema B-type lamps are ideal for today's demanding 3D and 2D digital cinema presentations. They are especially designed for Barco projectors. There is a choice of three power ratings in the B-type Digital Xenon Cinema lamps range: 3000W, 4000W, or 6500W. There is also a choice of three power ratings in the BH-type Digital Helios lamps: 2000W, 3000W, and 4200W power ratings. All these lamps produce the very high light output needed to maximize screen brightness and enhance the dramatic effect for the viewer. These long-life digital lamps also provide constant color temperature characteristics, and meet all of the stringent arc-stability requirements for consistent customer satisfaction. In addition to B-type Digital Cinema Xenon lamps there are C-, N-, S-, and TA-type Digital Cinema Xenon lamps. These are all individually customized per projector, so there is a different, perfect-fitting lamp for each projector model to ensure optimized projector performance.

Produkt Daten

Allgemeine Eigenschaften		Spannung (Nom)	
Betriebsstellung	P15 [Horizontal +/-15°]	35 V	
Hauptanwendungsgebiet	Cinema	Produktdaten	
Nennlebensdauer (Nom)	600 h	Gesamt-Produktcode	871829124944300
Magnet	-	Bestell-Produktname	XDC 6000 B
Elektrische Kenndaten		EAN/UPC - Produkt	8718291249443
Power (Rated) (Nom)	6000 W	Bestellcode	24944300
Lampenstrom	140/175 A	Anzahl pro Verpackung	1
Lampenstrom (Nom)	170 A	Anzahl pro Umverpackung	1
Zündimpulsspannung (max.)	36000 V	Material-Nr. (12NC)	928417606301
		Nettogewicht (Einzelteil)	1,140 kg

Abmessungsskizzen



LTIX XDC 6000 B

Product	O	D	X	B (max)	C (max)	A
XDC 6000 B	7,0 mm	70 mm	152 mm	393 mm	433 mm	170,5 mm

