

NEC digital cinema projectors


XDC 4002N

Digital Xenon Cinema N-type lamps are ideal for today's demanding 3D and 2D digital cinema presentations. They are especially designed for NEC projectors. There is a choice of three power ratings in the N-type Digital Cinema Xenon lamps range: 4000W, 4500W or 6000W. There is also a choice of three power ratings in the NH-type Digital Helios lamps range: 2000W, 300W, and 4200W. All these lamps produce the very high light output needed to maximize screen brightness and enhance the dramatic effect for the viewer. These long-life digital lamps also provide constant color temperature characteristics, and meet all of the stringent arc-stability requirements for consistent customer satisfaction. In addition to N-type Digital Cinema Xenon lamps there are B-, C-, S-, and TA-type Digital Cinema Xenon lamps. These are all individually customized per projector, so there is a different, perfect-fitting lamp for each projector model to ensure optimized projector performance.

Product data

General Information		Voltage (Nom)	
Operating position	P15 [Parallel +/-15D or Horizontal(HOR)]	32 V	
Main application	Cinema	Product Data	
Nominal lifetime (nom.)	1000 h	Full product code	871829168870900
Magnet	-	Order product name	XDC 4002N
Operating and Electrical		EAN/UPC – product	8718291688709
Power (Rated) (Nom)	4002 W	Order code	68870900
Lamp current span	95/125 A	Local Code	XDC4002N
Lamp current (nom.)	125 A	Numerator – quantity per pack	1
Ignition peak voltage (max.)	35000 V	Numerator – packs per outer box	1
		Material no. (12NC)	928418006301
		Net weight (piece)	0.625 kg

Dimensional drawing



LTIX XDC 4002 N

Product	O	D	X	B (max)	C (max)	A
XDC 4002N	6.1 mm	60 mm	160 mm	306 mm	336 mm	144 mm

