

Barco digital cinema projectors


XDC-1200B

Digital Xenon Cinema B-type lamps are ideal for today's demanding 3D and 2D digital cinema presentations. They are especially designed for Barco projectors. There is a choice of three power ratings in the B-type Digital Xenon Cinema lamps range: 3000W, 4000W, or 6500W. There is also a choice of three power ratings in the BH-type Digital Helios lamps: 2000W, 3000W, and 4200W power ratings. All these lamps produce the very high light output needed to maximize screen brightness and enhance the dramatic effect for the viewer. These long-life digital lamps also provide constant color temperature characteristics, and meet all of the stringent arc-stability requirements for consistent customer satisfaction. In addition to B-type Digital Cinema Xenon lamps there are C-, N-, S-, and TA-type Digital Cinema Xenon lamps. These are all individually customized per projector, so there is a different, perfect-fitting lamp for each projector model to ensure optimized projector performance.

Produkt Daten

Allgemeine Eigenschaften		Spannung (Nom)		20 V
Betriebsstellung	P5 [Horizontal +/-5°]	Produktdaten		
Hauptanwendungsgebiet	Cinema	Gesamt-Produktcode	871829176659900	
Nennlebensdauer (Nom)	3000 h	Bestell-Produktname	XDC-1200B	
Magnet	-	EAN/UPC - Produkt	8718291766599	
Elektrische Kenndaten		Bestellcode	76659900	
Power (Rated) (Nom)	1200 W	Anzahl pro Verpackung	1	
Lampenstrom	50/70 A	Anzahl pro Umverpackung	1	
Lampenstrom (Nom)	60 A	Material-Nr. (12NC)	928418506301	
Zündimpulsspannung (max.)	40000 V	Nettogewicht (Einzelteil)	400,000 g	

Abmessungsskizzen



LTIX XDC 1200 B

Product	O	D	X	B (max)	C (max)	A
XDC-1200B	4,7 mm	46 mm	132 mm	294 mm	343 mm	123 mm

