



MASTER SON-T PIA Plus 高壓鈉燈

MSTSON-TPIA Plus 70W E27 1CT/12

本產品為高壓鈉燈管，採用 透明外管，具有高輸出、品質穩定、以及使用壽命長等特色

安全提示

- Control gear must include end-of-life protection (IEC60662, IEC 62035)
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

产品数据

一般資訊	
燈座基底	E27 [E27]
操作位置	UNIVERSAL [任何或通用 (U)]
通量測量參考	Sphere
壽命 (故障率 50%) (標稱)	28,000 h
照明技術	
色碼	220 [CCT of 2000K]
光通量	6,650 lm
色度坐標 X (標稱)	0.54
色度坐標 Y (Nom)	0.42
相關色彩溫度 (規範)	1900 K
光效 (額定) (標準)	91 lm/W
演色性指數 (CRI)	-
運轉與電力	
耗電量	74.0 W
電壓 (標稱)	93 V


電壓 (標稱)	93 V
控制與調光	
可調光	是
機械與外罩	
燈泡表層	透明
燈泡形狀	T35 [T 35mm]
認證與應用	
節能省電等級	G
汞 (Hg) 含量 (最大)	12.2 mg
汞 (Hg) 含量 (標稱)	12.2 mg
能源消耗 kWh/1000 h	73 kWh
EPREL 註冊碼	1612144
產品資料	
下訂產品名稱	MSTSON-TPIA Plus 70W E27 1CT/12

MASTER SON-T PIA Plus 高壓鈉燈

完整產品名稱	MSTSON-TPIA Plus 70W E27 1CT/12
完整產品代碼	871829118069200
訂單代碼	928483200094
材質 Nr. (12NC)	928483200094
分子 - 每個包裝的數量	1


EAN/UPC - 產品/案例	8718291180692
分子 - 每一外盒包裝	12
EAN/UPC - 箱	8718291180708

二维绘图




Product	D (max)	O	L	C (max)
MSTSON-TPIA Plus 70W E27 1CT/12	35.75 mm	42 mm	102 mm	156 mm

光度数据




Light Distribution Diagram - MSTSON-TPIA Plus 70W E27 1CT/12




Spectral Power Distribution Colour - MSTSON-TPIA Plus 70W E27 1CT/12

壽命



Life Expectancy Diagram



Lumen Maintenance Diagram

MASTER SON-T PIA Plus 高壓鈉燈

