



Mercury Vapor Standard

H37KC-250/DX 3PK

Mercury Vapor lamps feature low initial cost, but have higher operating costs than HPS or Metal Halide due to its lower efficiency. The clear mercury bulb has a bluish green appearance and the Deluxe White has a higher color rendering. Mercury lamps get dimmer over time and rarely burn out, so it is wise to replace them and restore light level.

Warnings and Safety

- R "WARNING: These lamps can cause serious skin burn and eye inflammation from short wave ultraviolet radiation if outer envelope of the lamp is broken or punctured. Do not use where people will remain for more than a few minutes unless adequate shielding or other safety precautions are used. Certain lamps that will automatically extinguish when the outer envelope is broken or punctured are commercially available." This lamp complies with FDA radiation performance standard 21 CFR subchapter J. (USA:21 CFR 1040.30 Canada: SOR/DORS/80-381)
- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Product data


General Information		Correlated Color Temperature (Nom)	
Cap-Base	E39 [Single Contact Mogul Screw]	4100 K	
Operating Position	UNIVERSAL [Any or Universal (U)]	Luminous Efficacy (rated) (Nom)	
Life to 50% Failures (Nom)	15,000 hour(s)	48 lm/W	
Light Technical		Operating and Electrical	
Color Code	542 [CCT of 4200K]	Power Consumption	250.0 W
Color Designation	Cool White (CW)	Voltage (Nom)	135 V
Chromaticity Coordinate X (Nom)	380	Voltage (Nom)	135 V
Chromaticity Coordinate Y (Nom)	385		

Mercury Vapor Standard

Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Coated glass
Bulb Material	Hard Glass
Bulb Shape	ED90 [ED 90mm]
Approval and Application	
Mercury (Hg) Content (Nom)	38 mg


Product Data	
Order product name	HPL-N 250W E39/41 HG.1CT/3
Full product name	H37KC-250/DX 3PK
Order code	140806
Material Nr. (12NC)	928485100093
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677253530
Numerator - Packs per outer box	3
EAN/UPC - Case	50046677140804

Dimensional drawing




Product	D (max)	C (max)
HPL-N 250W E39/41 HG.1CT/3	91 mm	211 mm

Photometric data




Light Distribution Diagram - HPL-N 250W E39/41 HG.1CT/3




Spectral Power Distribution Colour - HPL-N 250W E39/41 HG.1CT/3

Mercury Vapor Standard

Lifetime



Life Expectancy Diagram - HPL-N 250W E39/41 HG.1CT/3



Lumen Maintenance Diagram - HPL-N 250W E39/41 HG.1CT/3

