



Mercury Vapor Standard

H33GL-400/DX FULL CT 6PK

Mercury Vapor lamps feature low initial cost, but have higher operating costs than HPS or Metal Halide due to its lower efficiency. The clear mercury bulb has a bluish green appearance and the Deluxe White has a higher color rendering. Mercury lamps get dimmer over time and rarely burn out, so it is wise to replace them and restore light level.

Warnings and Safety

- R "WARNING: These lamps can cause serious skin burn and eye inflammation from short wave ultraviolet radiation if outer envelope of the lamp is broken or punctured. Do not use where people will remain for more than a few minutes unless adequate shielding or other safety precautions are used. Certain lamps that will automatically extinguish when the outer envelope is broken or punctured are commercially available." This lamp complies with FDA radiation performance standard 21 CFR subchapter J. (USA:21 CFR 1040.30 Canada: SOR/DORS/80-381)
- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Product data

General Information	
Cap-Base	E39 [Single Contact Mogul Screw]
Operating Position	UNIVERSAL [Any or Universal (U)]
Life to 50% Failures (Nom)	15,000 hour(s)

Light Technical	
Color Code	542 [CCT of 4200K]
Color Designation	Cool White (CW)
Chromaticity Coordinate X (Nom)	376
Chromaticity Coordinate Y (Nom)	385

Correlated Color Temperature (Nom)	4200 K
Luminous Efficacy (rated) (Nom)	53 lm/W
Color rendering index (CRI)	50

Operating and Electrical	
Power Consumption	400 W
Voltage (Nom)	140 V
Voltage (Nom)	140 V

Mercury Vapor Standard

Controls and Dimming

Dimmable	No
----------	----

Mechanical and Housing

Bulb Finish	Coated glass
Bulb Material	Hard Glass
Bulb Shape	ED120 [ED 120mm]


Approval and Application

Mercury (Hg) Content (Nom)	72 mg
----------------------------	-------

Product Data


Order product name	HPL-N 400W E39/41 HG.SLV/6
Full product name	H33GL-400/DX FULL CT 6PK
Order code	248427
Material Nr. (12NC)	928485300091
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677248420
Numerator - Packs per outer box	6
EAN/UPC - Case	50046677248425

Dimensional drawing



Product	D (max)	C (max)
HPL-N 400W E39/41 HG.SLV/6	4-13/16 inch	11-7/16 inch



Photometric data



Spectral Power Distribution Colour - HPL-N 400W E39/41 HG.SLV/6

Mercury Vapor Standard

Lifetime



Life Expectancy Diagram - HPL-N 400W E39/41 HG.SLV/6

Lumen Maintenance Diagram - HPL-N 400W E39/41 HG.SLV/6

