# **PHILIPS** Lighting



# Pulse Start Metal Halide Standard

## MH 150W/640 E26 CL 1SL/24

Philips Pulse Start Metal Halide Lamps offer an optimized metal halide system for greater efficiency and lumen maintenance.

#### Warnings and Safety

• R "WARNING: These lamps can cause serious skin burn and eye inflammation from short wave ultraviolet radiation if outer envelope of the lamp is broken or punctured. Do not use where people will remain for more than a few minutes unless adequate shielding or other safety precautions are used. Certain lamps that will automatically extinguish when the outer envelope is broken or punctured are commercially available." This lamp complies with FDA radiation performance standard 21 CFR subchapter J. (USA:21 CFR 1040.30 Canada: SOR/DORS/80-381)

#### **Product data**

General Information		Voltage (Nom)	95 V
Cap-Base	E26 [Single Contact Medium Screw]	Voltage (Nom)	95 V
Operating Position	H [Hanging or Base Up (BU)]		
Life to 50% Failures (Nom)	15,000 hour(s)	Controls and Dimming	
		Dimmable	No
Light Technical			
Color Code	640 [CCT of 4000K]	Mechanical and Housing	
Color Designation	Cool White (CW)	Bulb Finish	Clear
Chromaticity Coordinate X (Nom)	385	Bulb Shape	ED17
Chromaticity Coordinate Y (Nom)	390		
Correlated Color Temperature (Nom)	4000 K	Approval and Application	
Luminous Efficacy (rated) (Nom)	87 lm/W	Mercury (Hg) Content (Nom)	11 mg
Color rendering index (CRI)	65	Energy Consumption kWh/1000 h	165 kWh
Operating and Electrical		Product Data	
Power Consumption	155 W	Order product name	MH 150W/640 E26 CL 1SL/2

### Pulse Start Metal Halide Standard

Full product name	MH 150W/640 E26 CL 1SL/24	
Order code	928486000191	
Material Nr. (12NC)	928486000191	
Numerator - Quantity Per Pack	1	
EAN/UPC - Product/Case	046677137526	

Numerator - Packs per outer box	24
EAN/UPC - Case	50046677137521

#### Dimensional drawing



Product	D (max)	L (min)	C (max)
MH 150W/640 E26 CL 1SL/24	56 mm	83 mm	138 mm



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com 2023, September 22 - data subject to change