



SON-T

SON-T 250W E E40 SL/12

High Pressure Sodium lamp with clear tubular outer bulb

Warnings and Safety

- Control gear must include end-of-life protection (IEC60662, IEC 62035)
- Control gear must include end-of-life protection (IEC60662, IEC 62035)
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


General Information		Voltage (Nom)	
Cap-Base	E40	100 V	
Operating Position	UNIVERSAL [Any or Universal (U)]	Controls and Dimming	
Life to 50% Failures (Nom)	28,000 hour(s)	Dimmable	Yes
Light Technical		Mechanical and Housing	
Color Code	220 [CCT of 2000K]	Bulb Finish	Clear
Correlated Color Temperature (Nom)	2000 K	Bulb Shape	T46
Luminous Efficacy (rated) (Nom)	110 lm/W	Approval and Application	
Color rendering index (CRI)	-	Mercury (Hg) Content (Nom)	20.4 mg
Arc Length O (Nom)	66 mm	Energy Consumption kWh/1000 h	275 kWh
Operating and Electrical		Product Data	
Power Consumption	255 W	Order product name	SON-T 250W E E40 SL/12
Voltage (Nom)	100 V	Full product name	SON-T 250W E E40 SL/12

SON-T

Full product code	871829121288100
Order code	928487200098
Material Nr. (12NC)	928487200098
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291212881




Numerator - Packs per outer box	12
EAN/UPC - Case	8718291212898

Dimensional drawing



Product	D (max)	O	L	C (max)
SON-T 250W E E40 SL/12	47 mm	66 mm	158 mm	255 mm



Photometric data



Light Distribution Diagram - SON-T 250W E E40 SL/12

Spectral Power Distribution Colour - SON-T 250W E E40 SL/12

Lifetime



Life Expectancy Diagram - SON-T 250W E E40 SL/12

Lumen Maintenance Diagram - SON-T 250W E E40 SL/12

SON-T

