



SON-T

SON-T 400W E E40 SL/12

High Pressure Sodium lamp with clear tubular outer bulb

Warnings and Safety


- Control gear must include end-of-life protection (IEC60662, IEC 62035)
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information	
Cap-Base	E40
Operating Position	UNIVERSAL [Any or Universal (U)]
Life to 50% Failures (Nom)	28,000 h
Light Technical	
Color Code	220 [CCT of 2000K]
Correlated Color Temperature (Nom)	2000 K
Luminous Efficacy (rated) (Nom)	123 lm/W
Color rendering index (CRI)	-
Arc Length O (Nom)	82 mm
Operating and Electrical	
Power Consumption	392.0 W
Voltage (Nom)	100 V
Voltage (Nom)	100 V
Controls and Dimming	
Dimmable	Yes




Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	T46
Approval and Application	
Mercury (Hg) Content (Nom)	24.5 mg
Energy Consumption kWh/1000 h	431 kWh
Product Data	
Order product name	SON-T 400W E E40 SL/12
Full product name	SON-T 400W E E40 SL/12
Full product code	871829121292800
Local code description	SONT400WGES
Order code	928487300098
Material Nr. (12NC)	928487300098
Local order code	SONT400WGES
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291212928
Numerator - Packs per outer box	12
EAN/UPC - Case	8718291212935

Dimensional drawing



Product	D (max)	O	L	C (max)
SON-T 400W E E40 SL/12	47 mm	82 mm	175 mm	286 mm



Photometric data



Light Distribution Diagram - SON-T 400W E E40 SL/12

Spectral Power Distribution Colour - SON-T 400W E E40 SL/12

Lifetime



Life Expectancy Diagram - SON-T 400W E E40 SL/12

Lumen Maintenance Diagram - SON-T 400W E E40 SL/12

