



SON-T

SON-T 1000W E E40 1SL/4

High Pressure Sodium lamp with clear tubular outer bulb

Warnings and Safety

- Control gear must include end-of-life protection (IEC60662, IEC 62035)
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


Product data

General Information	
Cap-Base	E40
Operating Position	UNIVERSAL [Any or Universal (U)]
Life to 50% Failures (Nom)	20,000 hour(s)
Light Technical	
Color Code	220 [CCT of 2000K]
Correlated Color Temperature (Nom)	2000 K
Luminous Efficacy (rated) (Nom)	130 lm/W
Color rendering index (CRI)	-
Arc Length O (Nom)	145 mm
Operating and Electrical	
Power Consumption	960.0 W
Voltage (Nom)	100 V
Voltage (Nom)	100 V
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	T65
Approval and Application	
Mercury (Hg) Content (Nom)	22.65 mg
Energy Consumption kWh/1000 h	1056 kWh
Product Data	
Order product name	SON-T 1000W E E40 1SL/4
Full product name	SON-T 1000W E E40 1SL/4
Full product code	871150021060945
Order code	928487400091
Material Nr. (12NC)	928487400091
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500210609
Numerator - Packs per outer box	4
EAN/UPC - Case	8711500210616



SON-T

Dimensional drawing



Product	D (max)	O	L	C (max)
SON-T 1000W E E40 1SL/4	66 mm	145 mm	240 mm	390 mm



Photometric data



Light Distribution Diagram - SON-T 1000W E E40 1SL/4

Spectral Power Distribution Colour - SON-T 1000W E E40 1SL/4

Lifetime



Life Expectancy Diagram - SON-T 1000W E E40 1SL/4

Lumen Maintenance Diagram - SON-T 1000W E E40 1SL/4

SON-T

