



MSD Platinum (Touring/Stage)

MSD Platinum 20 RB 1CT/8

The MSD Platinum lamps open up new levels of creative freedom in entertainment lighting, with powerful, compact and brilliantly intense light. Their compact, lightweight design provides the freedom to create smaller, lighter luminaires – for use at any location on stage. And their short arc, high color temperature and innovative reflector produce a sparkling, high beam intensity for outstanding color reproduction. They also offer long and reliable lifetime, high efficacy and fast replacement times. It all adds up to an intensely exciting creative experience.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information	
Cap-Base	-
Operating Position	UNIVERSAL [Any or Universal (U)]
Life to 50% Failures (Nom)	1,500 hour(s)
Light Technical	
Color Code	2
Luminous Flux	22,400 lm
Chromaticity Coordinate X (Nom)	296
Chromaticity Coordinate Y (Nom)	298
Correlated Color Temperature (Nom)	8000 K
Luminous Efficacy (rated) (Nom)	47 lm/W


Arc Length O (Nom)	1.2 mm
Operating and Electrical	
Power Consumption	470 W
Controls and Dimming	
Dimmable	Yes
Product Data	
Order product name	MSD Platinum 20 RB 1CT/8
Full product name	MSD Platinum 20 RB 1CT/8
Full product code	871869668420700
Order code	928495205314

MSD Platinum (Touring/Stage)

Material Nr. (12NC)	928495205314
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696684207
Numerator - Packs per outer box	8

EAN/UPC - Case	8718696684214
----------------	---------------

Dimensional drawing



Product	D (max)	O	C (max)
MSD Platinum 20 RB 1CT/8	58.5 mm	1.2 mm	72 mm

