

# PHILIPS

## Lighting



# MSD Platinum (Touring/Stage)

## MSD Platinum 20 RB 1CT/8

The MSD Platinum lamps open up new levels of creative freedom in entertainment lighting, with powerful, compact and brilliantly intense light. Their compact, lightweight design provides the freedom to create smaller, lighter luminaires – for use at any location on stage. And their short arc, high color temperature and innovative reflector produce a sparkling, high beam intensity for outstanding color reproduction. They also offer long and reliable lifetime, high efficacy and fast replacement times. It all adds up to an intensely exciting creative experience.

### Product data

General Information	
Base	- [-]
Operating Position	Universal [ Universal]
Main Application	Stage/Touring
Life to 50% Failures (Nom)	1500 h
System Description	Reflector E21.9 TCM

Light Technical	
Color Code	2
Initial lumen (Nom)	22400 lm
Chromaticity Coordinate X (Max)	314
Chromaticity Coordinate X (Min)	280
Chromaticity Coordinate X (Nom)	296
Chromaticity Coordinate Y (Max)	316
Chromaticity Coordinate Y (Min)	290
Chromaticity Coordinate Y (Nom)	298
Correlated Color Temperature (Nom)	8000 K

Operating and Electrical	
Luminous Efficacy (rated) (Nom)	47 lm/W
Power (Rated) (Nom)	470 W
Voltage (Max)	110 V
Voltage (Min)	85 V

Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Cap-Base Information	na [-]

Luminaire Design Requirements	
Bulb Temperature (Max)	900 °C
Pinch Temperature (Max)	350 °C

## MSD Platinum (Touring/Stage)


### Product Data

XUCDM.COPY.Product.Title	MSD Platinum 20 RB 1CT/8
EAN/UPC - Product	8718696684207
Order code	323741
Numerator - Quantity Per Pack	1

Numerator - Packs per outer box	8
Material Nr. (12NC)	928495205314
Net Weight (Piece)	136.600 g

### Warnings and Safety

### Dimensional drawing



MSD Platinum 20 RB

Product	D (max)	O	C (max)
MSD Platinum 20 RB 1CT/8	58.5 mm	1.2 mm	72 mm

